



**Wattstopper**  
**Discontinued - Digital PIR 1-Button Wall Mount Sensor w/Infrared, Grey**  
 Part No. LMPW-101-G



LMPW-100 Series Digital PIR Wall Switch Occupancy Sensors use passive infrared (PIR) technology to detect occupancy for energy-efficient control of lighting and plug loads. They also include one or two switch buttons for manual control of selected loads, and are part of a Wattstopper Digital Lighting Management (DLM) system

## Features & Benefits

1-button Digital PIR Wall Switch Occupancy Sensor

LMPW-100 Series Digital PIR Wall Switch Occupancy Sensors use passive infrared (PIR) technology to detect occupancy for energy-efficient control of lighting and plug loads

They also include one or two switch buttons for manual control of selected loads, and are part of a Wattstopper Digital Lighting Management (DLM) system

Passive infrared sensor with On/Off button(s) to switch selected load(s)

Component of Digital Lighting Management integrated control system

Quick access to Push n' Learn for system personalization

Digital sensor with LCD display and programming pushbuttons

IR transceiver for wireless configuration and remote control

Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors

## Specifications

### General Info

Product Line	Wattstopper	Color	Gray
Finish	Glossy	UPC Number	754182932252
Country Of Origin	China	Product Series	LMPW-100
Features	Adjustable Time Delay, Indicator Lights, Load Controller Required, Sensitivity Adjustment	Switch Type	Motion Sensor, Push
Number of Switches	1	Installation Location	Wall
Included	Mounting Screws	Application Sector	Commercial
Standard	UL, cUL, FCC part 15, RoHS	Warranty Type	5-Year

---

Type	Sensor, Switch
------	----------------

---

## Dimensions

---

Product Width US	1.8 in	Product Weight US	0.2 lb
------------------	--------	-------------------	--------

---

Product Volume US	20.3 cu in	Product Depth US	1.9 in
-------------------	------------	------------------	--------

---

Product Height US	4.1 in
-------------------	--------

---

## Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

## Technical Information

---

Operating Temperature Min	32 °F	Timer Type	Digital
---------------------------	-------	------------	---------

---

Compatibility	DLM Wired, Infrared Wireless	Has Battery	No
---------------	------------------------------	-------------	----

---

Sensor Coverage Pattern	180 deg	Sensor Type	Occupancy
-------------------------	---------	-------------	-----------

---

Operating Temperature Max	131 °F	Sensor Mounting Height	4 ft
---------------------------	--------	------------------------	------

---

Number of Buttons	1	Number of Rockers	0
-------------------	---	-------------------	---

---

Sensor Technology	Passive Infrared (PIR)	Timer Duration	1-30 Minutes
-------------------	------------------------	----------------	--------------

---

Topology	Free Topology	Indicator	Button LED, PIR Detection LED, Sensor Binding (PNL) LED
----------	---------------	-----------	---

---

Input Voltage	24 VDC	Indoor/Outdoor	Indoor
---------------	--------	----------------	--------

---

Mounting Type	In-Wall	On Function	Selectable Auto/Manual
---------------	---------	-------------	------------------------

---

Current Draw	8 mA	Operating Temperature	0°-55°C, 32°-131°F
--------------	------	-----------------------	--------------------

---

Operating Humidity	5-95% RH (Non-Condensing)	Sensing Range	40 ft radius
--------------------	---------------------------	---------------	--------------

---

Wire Connection Type	RJ-45	Engraving Type	Blank
----------------------	-------	----------------	-------

---

Storage Temperature	23° - 176° F, -5° - 80° C
---------------------	---------------------------

---