



Wattstopper
DLM WIRED SHADE SWITCH 2B 2R W HITE
Part No. LMSH-SW222-W



LMSH-SW2xx Series Wall Switches are low voltage devices for manual control of shades from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any shade motors connected to DLM shade controllers

Features & Benefits

Switches are pre-engraved with most common control configurations

Low voltage pushbutton switches for control of multiple shades

Plug n' Go automatic configuration along with Pull n' Save and Push n' Learn for system personalization

Plug to other components using Cat 5e cables with RJ45connectors eliminating wiring errors

Matches 200-Series DLM lighting control switches for consistent design of lighting and shade control

Includes system configuration button for easy system programming from the switch

IR transceiver for wireless configuration and remote control

Components of Digital Lighting Management integrated shade control system

Custom engraving or engraved and non-engraved button kits available

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Matte	UPC Number	754182948932
Country Of Origin	China	Product Series	LMSW-SH
Switch Type	Push, Rocker	Number of Switches	2
Application Sector	Commercial	Standard	UL, cUL, FCC part 15, RoHS
Warranty Type	5-Year	Type	Switch

Dimensions

Product Width US	1.6 in	Product Weight US	0.1 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		

Technical Information

Operating Temperature Min	0 °C	Compatibility	DLM Wired
Has Battery	No	Operating Temperature Max	55 °C
Number of Buttons	2	Number of Rockers	2
Topology	Free Topology	Input Voltage	24 VDC
Indoor/Outdoor	Indoor	Mounting Type	J-Box
Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
Engraving Type	Icon with Text	Storage Temperature	23° - 176° F, -5° - 80° C