



## Wattstopper Discontinued - Digital Switch, 2-button w/infrared, White Part No. LMSW-102-W



LMSW-100 Series Wall Switches are low voltage devices for energy-saving manual on/off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

### Features & Benefits

Low voltage pushbutton switches for control of multiple loads

Components of Digital Lighting Management integrated control system

Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors

Customizable buttons with LED status indicators

IR transceiver for wireless configuration and remote control

Plug n' Go automatic configuration and Push n' Learn for personalization

### Specifications

#### General Info

Product Line	Wattstopper	Replaced by Part Number	LMSW-220-W
Color	White	Finish	Glossy
UPC Number	754182925452	Country Of Origin	China
Product Series	LMSW	Switch Type	Push
Number of Switches	2	Application Sector	Commercial
Standard	UL, cUL, FCC part 15, RoHS	Warranty Type	5-Year
Type	Switch		

#### Dimensions

---

Product Width US	1.8 in	Product Weight US	0.2 lb
------------------	--------	-------------------	--------

---

Product Volume US	20.3 cu in	Product Depth US	1.6 in
-------------------	------------	------------------	--------

---

Product Height US	4.1 in
-------------------	--------

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Operating Temperature Min	0 °C	Compatibility	DLM Wired
---------------------------	------	---------------	-----------

---

Has Battery	No	Operating Temperature Max	55 °C
-------------	----	---------------------------	-------

---

Number of Buttons	2	Number of Rockers	0
-------------------	---	-------------------	---

---

Topology	Free Topology	Input Voltage	24 VDC
----------	---------------	---------------	--------

---

Indoor/Outdoor	Indoor	Mounting Type	J-Box
----------------	--------	---------------	-------

---

Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
--------------	------	-----------------------	--------------------

---

Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
--------------------	---------------------------	----------------------	-------

---

Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C
----------------	-------	---------------------	---------------------------

---