




Wattstopper
Discontinued - SCENE SWITCH 5 ENGRAVED - ON OFF SCENES TEACHING - WHITE
Part No. LMSW-105-W-ENG4



LMSW-100 Series Digital Wall Switches are low voltage devices for energy-saving manual on/ off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

Features & Benefits

5-Button Wall Switch

LMSW-100 Series Digital Wall Switches are low voltage devices for energy-saving manual on/ off control of one or more loads from one or more locations

They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers

Low voltage pushbutton switches for control of multiple loads

Each button can control individual or multiple loads, or one scene

Plug to other components using Cat 5e cable and RJ45 connectors eliminating wiring errors

Customizable buttons with LED status indicators

IR transceiver for wireless configuration and remote control

Plug n' Go automatic configuration and Push n' Learn for personalization

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182945566
Country Of Origin	China	Product Series	LMSW
Switch Type	Push	Number of Switches	5
Application Sector	Commercial	Standard	UL, cUL, FCC part 15, RoHS
Warranty Type	5-Year	Type	Switch

Dimensions

Product Width US	1.8 in	Product Weight US	0.1861 lb
------------------	--------	-------------------	-----------

Product Volume US	19.845 cu in	Product Depth US	1.6 in
-------------------	--------------	------------------	--------

Product Height US	4.2 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	0 °C	Compatibility	DLM Wired
---------------------------	------	---------------	-----------

Has Battery	No	Operating Temperature Max	55 °C
-------------	----	---------------------------	-------

Number of Buttons	5	Number of Rockers	0
-------------------	---	-------------------	---

Topology	Free Topology	Input Voltage	24 VDC
----------	---------------	---------------	--------

Indoor/Outdoor	Indoor	Mounting Type	J-Box
----------------	--------	---------------	-------

Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
--------------	------	-----------------------	--------------------

Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
--------------------	---------------------------	----------------------	-------

Engraving Type	Text	Storage Temperature	23° - 176° F, -5° - 80° C
----------------	------	---------------------	---------------------------
