



## Wattstopper Discontinued - Digital Switch, 8-button w/infrared, Ivory, USA Part No. LMSW-108-IU



LMSW-100 Series Wall Switches are low voltage devices for energy-saving manual on/off control of one or more loads from one or more locations. They are part of a Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

### Features & Benefits

Low voltage pushbutton switches for control of multiple loads	Components of Digital Lighting Management integrated control system
Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors	Customizable buttons with LED status indicators
IR transceiver for wireless configuration and remote control	Plug n' Go automatic configuration and Push n' Learn for personalization

### Specifications

#### General Info

Product Line	Wattstopper	Color	Ivory
Finish	Glossy	UPC Number	754182927784
Country Of Origin	United States	Product Series	LMSW
Switch Type	Push	Number of Switches	8
Application Sector	Commercial	Standard	UL, cUL, FCC part 15, RoHS, BAA, TAA
Warranty Type	5-Year	Type	Switch

#### Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
------------------	--------	-------------------	--------

---

Product Volume US	20.3 cu in	Product Depth US	1.6 in
-------------------	------------	------------------	--------

---

Product Height US	4.1 in
-------------------	--------

---

### Technical Information

---

Operating Temperature Min	0 °C	Compatibility	DLM Wired
---------------------------	------	---------------	-----------

---

Has Battery	No	Number of Connections	2
-------------	----	-----------------------	---

---

Operating Temperature Max	55 °C	Number of Buttons	8
---------------------------	-------	-------------------	---

---

Number of Rockers	0	Topology	Free Topology
-------------------	---	----------	---------------

---

Input Voltage	24 VDC	Indoor/Outdoor	Indoor
---------------	--------	----------------	--------

---

Mounting Type	J-Box	Current Draw	5 mA
---------------	-------	--------------	------

---

Operating Temperature	0°-55°C, 32°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
-----------------------	--------------------	--------------------	---------------------------

---

Wire Connection Type	RJ-45	Engraving Type	Blank
----------------------	-------	----------------	-------

---

Storage Temperature	23° - 176° F, -5° - 80° C
---------------------	---------------------------

---