



Wattstopper DLM PLUGLOAD CONTROLLER 20A METERED

Part No. LMPL-111-20M



The LMPL-111-20M Plug Load Controller contains a 20 amp relay for on/ off control of connected outlets, and a highefficiency intelligent switching power supply. This plug load controller works as part of the Wattstopper Digital Lighting Management (DLM) system and enables energy-efficient control of plug loads.

Features & Benefits

Plenum-rated controller with line voltage relay and intelligent switching power supply

Knockout mounting for easy installation

Advanced real time metering of voltage and current (+/- 2% accuracy)

Plug n' Go™ automatic configuration for quick installation and maximum energy efficiency

Accepts occupancy sensor signal or schedule events for energy saving control of plug load

Plugs to other components using Cat 5e cable and RJ45 connectors eliminating wiring errors

Specifications

General Info

| | | | |
|--------------------|-------------|-----------------------|---|
| Product Line | Wattstopper | Color | White |
| Finish | Glossy | UPC Number | 754182944200 |
| Country Of Origin | China | Product Series | LMPL |
| Features | Metered | Installation Location | Ceiling |
| Application Sector | Commercial | Standard | UL 88T9, UL 2043, cUL, FCC part 15, PEP, RoHS |
| Warranty Type | 5-Year | Type | Room Controller |

Dimensions

| | | | |
|------------------|--------|-------------------|--------|
| Product Width US | 3.9 in | Product Weight US | 0.6 lb |
|------------------|--------|-------------------|--------|

| | | | |
|-------------------|------------|------------------|--------|
| Product Volume US | 44.6 cu in | Product Depth US | 2.0 in |
|-------------------|------------|------------------|--------|

| | |
|-------------------|--------|
| Product Height US | 4.4 in |
|-------------------|--------|

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|---------------------------|-------|----------------|--------|
| Operating Temperature Min | 32 °F | Output Voltage | 24 VDC |
|---------------------------|-------|----------------|--------|

| | | | |
|-------------|----------------|---------------|-----------|
| Load Rating | 20 A @ 120 VAC | Compatibility | DLM Wired |
|-------------|----------------|---------------|-----------|

| | | | |
|-------------|----|-----------------------|---|
| Has Battery | No | Number of Connections | 2 |
|-------------|----|-----------------------|---|

| | | | |
|-----------------------|--------|---------------------------|--------|
| Dimming Compatibility | On/Off | Operating Temperature Max | 131 °F |
|-----------------------|--------|---------------------------|--------|

| | | | |
|----------|---------------|------------------|---|
| Topology | Free Topology | Number of Relays | 1 |
|----------|---------------|------------------|---|

| | | | |
|---------------|-------|----------------|--------------|
| Input Voltage | 120 V | Line Frequency | 50 Hz, 60 Hz |
|---------------|-------|----------------|--------------|

| | | | |
|----------------|--------|---------------|----------------------------------|
| Indoor/Outdoor | Indoor | Mounting Type | 1/2 in Knockout, 4 in Deep J-Box |
|----------------|--------|---------------|----------------------------------|

| | | | |
|-----------------------|--------------------|--------------------|---------------------------|
| Operating Temperature | 0°-55°C, 32°-131°F | Operating Humidity | 5-95% RH (Non-Condensing) |
|-----------------------|--------------------|--------------------|---------------------------|

| | | | |
|----------------------|-------|---------------------|--------------|
| Wire Connection Type | RJ-45 | Storage Temperature | 23° - 176° F |
|----------------------|-------|---------------------|--------------|
