



## Wattstopper Digital Enhanced Plug Load Controller, On/Off, 120V, 60Hz Part No. LMPL-201



LMPL-201 Plug Load Controllers include a 20 amp relay for on/ off control of connected outlets, and a high-efficiency switching power supply. They are part of a Wattstopper Digital Lighting Management (DLM) system, and enable energy-efficient control of plug loads.

### Features & Benefits

Plenum-rated controller with line voltage relay and switching power supply	Component of Digital Lighting Management integrated control systems
Plugs to other components using Cat 5e cable and RJ45 connectors eliminating wiring errors	Plug n' Go automatic configuration and Push n' Learn for personalization
Integral current monitoring of total connected load	Accepts occupancy sensor signal for energy saving control of plug loads

### Specifications

#### General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182928842
Country Of Origin	China	Product Series	LMPL
Installation Location	Ceiling	Application Sector	Commercial
Standard	UL 88T9, UL 2043, cUL, FCC part 15, PEP, RoHS	Warranty Type	5-Year
Type	Room Controller		

#### Dimensions

Product Width US	6.5 in	Product Weight US	1.5 lb
------------------	--------	-------------------	--------

---

Product Volume US	231.0 cu in	Product Depth US	3.0 in
-------------------	-------------	------------------	--------

---

Product Height US	6.5 in
-------------------	--------

---

### Additional Information

---

RoHS Compliant	Yes
----------------	-----

---

### Technical Information

---

Operating Temperature Min	32 °F	Output Voltage	24 VDC
---------------------------	-------	----------------	--------

---

Load Rating	20 A @ 120 VAC	Compatibility	DLM Wired
-------------	----------------	---------------	-----------

---

Has Battery	No	Number of Connections	4
-------------	----	-----------------------	---

---

Dimming Compatibility	On/Off	Operating Temperature Max	158 °F
-----------------------	--------	---------------------------	--------

---

Topology	Free Topology	Number of Relays	1
----------	---------------	------------------	---

---

Input Voltage	120 V	Line Frequency	50 Hz, 60 Hz
---------------	-------	----------------	--------------

---

Indoor/Outdoor	Indoor	Mounting Type	4 in Deep J-Box
----------------	--------	---------------	-----------------

---

Operating Temperature	0°-70°C, 32°-158°F	Operating Humidity	5-95% RH (Non-Condensing)
-----------------------	--------------------	--------------------	---------------------------

---

Wire Connection Type	RJ-45	Storage Temperature	23° - 176° F
----------------------	-------	---------------------	--------------

---