



Wattstopper
DLM Wired Standard Switch, 1B, White
Part No. LMSW-210-W



LMSW-200 Series Wall Switches are programmable, low voltage devices for manual on/off, dimming, and scene control of one or more loads from one or more locations. They are part of the Digital Lighting Management (DLM) system and can control any load(s) connected to DLM room controllers.

Features & Benefits

Software lockable configuration button, accessible without faceplate removal

Infrared (IR) transceiver for wireless configuration and control

Each button and rocker can control individual or multiple loads. Buttons can instead control one scene. LED indicates status.

Custom engraving available to replace standard engraving

The product meets the materials restrictions of RoHS

Digital Lighting Management components plug together on a free-topology Category 5e DLM local network

Switches may be used for multi-way control

Each button can be used to dim assigned loads

Sleek single gang devices fit decorator wall plates

BAA compliant options available

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182948710	Country Of Origin	China
Features	Pre-Engraved	Switch Type	Push
Number of Switches	1	Package Quantity	1
Application Sector	Commercial	Standard	UL and cUL
Warranty Type	5-Year		

Dimensions

Product Width US	1.6 in	Product Weight US	0.1 lb
------------------	--------	-------------------	--------

Product Volume US	19.85 cu in	Product Depth US	1.6 in
-------------------	-------------	------------------	--------

Product Height US	4.1 in	Product Length US	1.7 in
-------------------	--------	-------------------	--------

Additional Information

Product Has Potential to Contribute to LEED	Yes
---	-----

Technical Information

Compatibility	DLM	Actuator	Push
---------------	-----	----------	------

Number of Gangs	1	Number of Buttons	1
-----------------	---	-------------------	---

Action	Set intensity of light level	Indicator	DLM programming tools
--------	------------------------------	-----------	-----------------------

Indoor/Outdoor	Indoor	Wattage	0.168 W
----------------	--------	---------	---------

Mounting Type	Box	Supply Voltage	24 VDC
---------------	-----	----------------	--------

Operating Temperature	0°-55°C	Voltage	24.0 V
-----------------------	---------	---------	--------

Connection Type	Plug-In	Environmental Conditions	5 to 95%
-----------------	---------	--------------------------	----------
