



## Wattstopper LP8 Peanut Panel w/4 Relays, 115 /277 Volts, Surface Mount Part No. LP8S-4-115



Wattstopper's LP8 Peanut Lighting Control Panels provide simple, effective zone-based control of exterior and interior lighting in small applications. Panels control up to eight channels or zones of lighting. Zones respond to control signals from the system clock (or other signaling device) to turn lighting on and off. LP8 Panels ship pre-assembled in easy-to-install compact packages available for surface and flush mounting. They consist of relays, a system clock, panel intelligence, power supply, tub and cover. The standard enclosure is NEMA 1-rated.

### Features & Benefits

Simple and effective interior and exterior lighting control

Controls up to eight single-pole lighting circuits

Easy user interface with on-screen help

Compatible with AS-100 Automatic Control Switches for local override control

System clock provides time scheduled or astronomic control

### Specifications

#### General Info

Product Line	Wattstopper	Color	Black
Finish	Painted	UPC Number	754182914104
Country Of Origin	United States	Product Series	LP8
Features	8 Inputs for Low Voltage Switches, LCD Screen	Installation Location	Wall
Application Sector	Commercial	Warranty Type	1-Year
Type	Relay Panel		

#### Dimensions

Product Width US	16.5 in	Product Depth US	4.6 in
------------------	---------	------------------	--------

---

Product Height US	15.1 in
-------------------	---------

---

## Technical Information

---

Operating Temperature Min	32 °F	Output Voltage	24 VDC
---------------------------	-------	----------------	--------

---

Timer Type	Astronomical	Load Rating	20 A @ 120/347 VAC, 30 A @ 277 VAC
------------	--------------	-------------	---------------------------------------

---

Compatibility	AS-100, EM-24D2, LVSW	Horsepower Rating	1-1/2 HP @ 120 VAC
---------------	-----------------------	-------------------	--------------------

---

Bus Power Supply	800 mA @ 24 VDC	Operating Temperature Max	139 F
------------------	-----------------	---------------------------	-------

---

Enclosure Type	NEMA 1	Number of Poles	Single Pole
----------------	--------	-----------------	-------------

---

Number of Relays	4	Indicator	Relay Status LED
------------------	---	-----------	------------------

---

Input Voltage	115/277 VAC	Line Frequency	50 Hz, 60 Hz
---------------	-------------	----------------	--------------

---

Indoor/Outdoor	Indoor	Mounting Type	Screw Holes, Surface
----------------	--------	---------------	----------------------

---

Operating Temperature	32°-139°F	Operating Humidity	5-95% RH (Non-Condensing)
-----------------------	-----------	--------------------	---------------------------

---

Storage Temperature	23° - 176° F
---------------------	--------------

---