



**Wattstopper**  
**Discontinued - DLM 4-Button Partition Switch, Lt. Almond**  
Part No. LMPS-104-LA



The LMPS-104 Digital Partition Switch enables quick manual coordination of lighting controls in flexible spaces with up to four movable walls. It is part of a Digital Lighting Management (DLM) system, and can reconfigure connected switches and occupancy sensors. The LMPS-104 may also be used as a status indicator when an LMIO-102 Digital Partition Interface is used for automatic coordination of controls.

## Features & Benefits

### Digital Partition Switch

The LMPS-104 Digital Partition Switch enables quick manual coordination of lighting controls in flexible spaces with up to four movable walls

It is part of a Digital Lighting Management (DLM) system, and can reconfigure connected switches and occupancy sensors

The LMPS-104 may also be used as a status indicator when an LMIO-102 Digital Partition Interface is used for automatic coordination of controls.

Reconfigures lighting controls for logical operation when movable walls are opened and closed

Each button represents one wall- LED indicates status

Recalls 16 configurations for spaces with up to 5 partitioned areas and 4 movable walls

Infrared (IR) transceiver for wireless configuration and control

Sleek single gang device fits decorator wall plates

Five color options and custom engraving options- standard buttons may be replaced in the field

## Specifications

### General Info

Product Line	Wattstopper	Replaced by Part Number	LMPS-104-LA-U
Color	Light Almond	Finish	Glossy
UPC Number	754182940493	Country Of Origin	China
Product Series	LMPS	Switch Type	Push
Number of Switches	4	Application Sector	Commercial
Standard	UL, cUL, RoHS, FCC part 15	Warranty Type	5-Year
Type	Switch		

Dimensions

Product Width US	1.76 in	Product Weight US	0.2 lb
Product Volume US	11.98 cu in	Product Depth US	1.64 in
Product Height US	4.15 in		

Technical Information

Operating Temperature Min	0 °C	Compatibility	DLM Wired
Has Battery	No	Operating Temperature Max	55 °C
Number of Buttons	4	Number of Rockers	0
Topology	Free Topology	Input Voltage	24 VDC
Indoor/Outdoor	Indoor	Mounting Type	J-Box
Current Draw	5 mA	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	RJ-45
Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C