



Wattstopper
Discontinued - Digital PIR 1-Button Wall Mount Sensor w/Infrared, White
Part No. LMPW-101-W



LMPW-100 Series Digital PIR Wall Switch Occupancy Sensors use passive infrared (PIR) technology to detect occupancy for energy-efficient control of lighting and plug loads. They also include one or two switch buttons for manual control of selected loads, and are part of a Wattstopper Digital Lighting Management (DLM) system

Features & Benefits

1-button Digital PIR Wall Switch Occupancy Sensor

LMPW-100 Series Digital PIR Wall Switch Occupancy Sensors use passive infrared (PIR) technology to detect occupancy for energy-efficient control of lighting and plug loads

They also include one or two switch buttons for manual control of selected loads, and are part of a Wattstopper Digital Lighting Management (DLM) system

Passive infrared sensor with On/Off button(s) to switch selected load(s)

Component of Digital Lighting Management integrated control system

Quick access to Push n' Learn for system personalization

Digital sensor with LCD display and programming pushbuttons

IR transceiver for wireless configuration and remote control

Plug to other components using Cat 5e cables with RJ45 connectors eliminating wiring errors

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	LMDW-220-W
Color	White	Finish	Glossy
UPC Number	754182932214	Country Of Origin	China
Product Series	LMPW-100	Features	Adjustable Time Delay, Indicator Lights, Load Controller Required, Sensitivity Adjustment
Switch Type	Motion Sensor, Push	Number of Switches	1
Installation Location	Wall	Included	Mounting Screws
Application Sector	Commercial	Standard	UL, cUL, FCC part 15, RoHS

Warranty Type	5-Year	Type	Sensor, Switch
---------------	--------	------	----------------

Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	20.3 cu in	Product Depth US	1.9 in
Product Height US	4.2 in		

Additional Information

RoHS Compliant	Yes		
----------------	-----	--	--

Technical Information

Operating Temperature Min	32 °F	Timer Type	Digital
Compatibility	DLM Wired, Infrared Wireless	Has Battery	No
Sensor Coverage Pattern	180 deg	Sensor Type	Occupancy
Operating Temperature Max	131 °F	Sensor Mounting Height	4 ft
Number of Buttons	1	Number of Rockers	0
Sensor Technology	Passive Infrared (PIR)	Timer Duration	1-30 Minutes
Topology	Free Topology	Indicator	Button LED, PIR Detection LED, Sensor Binding (PNL) LED
Input Voltage	24 VDC	Indoor/Outdoor	Indoor
Mounting Type	In-Wall	On Function	Selectable Auto/Manual
Current Draw	8 mA	Operating Temperature	0°-55°C, 32°-131°F
Operating Humidity	5-95% RH (Non- Condensing)	Sensing Range	40 ft radius
Wire Connection Type	RJ-45	Engraving Type	Blank
Storage Temperature	23° - 176° F, -5° - 80° C		
