



Wattstopper Discontinued - DLM Wireless 5-Button Wall Switch, White Part No. LMSW-605-W



The LMSW-605 Scene Switch is a wireless device that can set and recall preset lighting scenes and raise and lower lighting levels. It is part of the wireless Digital Lighting Management (DLM) system and controls loads connected to DLM room controllers by recalling any four of the 16 scenes available in a DLM local network. It can function as a part of a completely wireless room pairing with a wireless room controller (LMRC-611MCC) or used in a hybrid wired & wireless room to control loads connected to a traditional wired room controllers when used in conjunction with a wireless bridge (LMBC-650).

Features & Benefits

Wireless Digital 5-Button Scene Switch

It is part of the wireless Digital Lighting Management (DLM) system and controls loads connected to DLM room controllers by recalling any four of the 16 scenes available in a DLM local network

Built-in IPv6 Wireless and Bluetooth antennas provide robust signal strength and reliable communication

Paddle with LED status indicator allows raise/lower control of scenes or loads

Ground wire allows you to install next to a line voltage device. This wire is only needed when placed next to a line voltage device in the same box. Grounding cables are otherwise not needed if in a purely low voltage application.

The LMSW-605 Scene Switch is a wireless device that can set and recall preset lighting scenes and raise and lower lighting levels

It can function as a part of a completely wireless room pairing with a wireless room controller (LMRC-611MCC)

Uses IPv6 wireless to establish network communication with DLM wireless devices

Quick and easy wireless installation – no Cat 5e connection needed

Low voltage switches for control of four customizable scenes

Specifications

General Info

Product Line	Wattstopper	Replaced by Part Number	LMSW-632-S-W, LMSW-622-S-W, LMSW-641-S-W
Color	White	Finish	Glossy
UPC Number	754182942923	Country Of Origin	China
Product Series	LMSW	Switch Type	Push
Number of Switches	5	Application Sector	Commercial

Standard	UL, cUL, FCC part 15, RoHS	Warranty Type	5-Year
Type	Switch		
Dimensions			
Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Operating Temperature Min	0 °C	Compatibility	DLM Wireless (IPv6), LMBC-650
Has Battery	Yes	Number of Connections	0
Battery Capacity	1500 mAh	Frequency Band	2.4 GHz
Operating Temperature Max	40 °C	Number of Buttons	5
Number of Rockers	0	Wireless Range	Bluetooth, up to 30 ft, IPv6 6LoWPAN, up to 60 ft
Topology	Wireless Mesh	Antenna	Integrated, Internal
Input Voltage	3 VDC	Indoor/Outdoor	Indoor
Battery Life	Up to 10 Years	Mounting Type	J-Box
Battery	CR123A 3V	Operating Temperature	0°-40°C, 32°-104°F
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	Wireless
Antenna Pattern	Omni-directional	Engraving Type	Blank
Encryption	AES 128-bit	Storage Temperature	23° - 140° F, -5° - 60° C