



Pass and Seymour  
Discontinued - LS Series Low-Voltage Slide Dimmer, Ivory  
Part No. LSLV600PI



Magnetic Low-Voltage Slide Dimmer, Preset 600VA

## Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise Electromagnetic and radio-frequency interference protection built in. control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

Superior heat management.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

No derating on 600W units.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |                    |             |
|-------------------|----------------|--------------------|-------------|
| Product Line      | Pass & Seymour | Color              | Ivory       |
| Country Of Origin | China          | Application Sector | Residential |
| Standard          | UL Listed      | Type               | Dimmer      |

### Listing Agencies / 3rd Party Agencies

|                     |       |              |     |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | 95219 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

---

## Technical Information

---

|                  |        |                 |             |
|------------------|--------|-----------------|-------------|
| Operating Cycles | 100000 | Number of Poles | Single Pole |
|------------------|--------|-----------------|-------------|

---

|         |       |         |         |
|---------|-------|---------|---------|
| Wattage | 600 W | Voltage | 120.0 V |
|---------|-------|---------|---------|

---

|      |          |
|------|----------|
| Load | 600 Watt |
|------|----------|

---