



## Wattstopper Low Voltage Wall Switch, 1-Button w/LED, Ivory Part No. LVSW-101-I



LVSW-100 Series Low Voltage Switches are lighting control devices that use conventional point-to-point low voltage wiring for control of single or multiple loads. Each button provides a momentary contact that is intended for use with compatible low voltage relay panels or similar lighting control panels or devices. Each button has an LED indicator that can serve as a status indicator or as a locator light.

### Features & Benefits

- Sleek single gang devices fit decorator wall plates (not supplied); 1-, 2-, 3-, 4-, and 8-button models
- Blue LED indicator on each button can be used as a locator light or as a status indicator
- Five color options and custom engraving options; standard buttons may be replaced in the field
- The product meets the materials restrictions of RoHS

### Specifications

#### General Info

Product Line	Wattstopper	Color	Ivory
Finish	Glossy	UPC Number	754182931323
Country Of Origin	China	Product Series	LVSW
Switch Type	Push	Number of Switches	1
Application Sector	Commercial	Standard	UL, cUL, RoHS
Warranty Type	5-Year	Type	Switch

#### Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		

#### Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	0 °C	Compatibility	LC8, LP8
Seismic Tested	No	Has Battery	No
Operating Temperature Max	55 °C	Number of Gangs	1
Number of Buttons	1	Input Voltage	24 VDC
Indoor/Outdoor	Indoor	Mounting Type	J-Box
Current Draw	2 mA	Operating Temperature	0°-55°C
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	Screw Terminal
Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C