



Wattstopper Low Voltage Switch, 3-Button w/LED, White Part No. LVSW-103-W



LVSW-100 Series Low Voltage Switches are lighting control devices that use conventional point-to-point low voltage wiring for control of single or multiple loads. Each button provides a momentary contact that is intended for use with compatible low voltage relay panels or similar lighting control panels or devices. Each button has an LED indicator that can serve as a status indicator or as a locator light.

Features & Benefits

Low voltage pushbutton switches for on/off control of one or more loads

Compatible with LC8, LP8, LI and LMCP Series lighting control panels

LED pilot light on each button

Customizable, field replaceable buttons

Single gang devices, compatible with standard decorator style face plates

Appearance matches DLM LMSW-100 Series digital wall switches

Specifications

General Info

Product Line	Wattstopper	Color	White
Finish	Glossy	UPC Number	754182931408
Country Of Origin	China	Product Series	LVSW
Switch Type	Push	Number of Switches	3
Application Sector	Commercial	Standard	UL, cUL, RoHS
Warranty Type	5-Year	Type	Switch

Dimensions

Product Width US	1.8 in	Product Weight US	0.2 lb
Product Volume US	20.3 cu in	Product Depth US	1.6 in
Product Height US	4.1 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	0 °C	Compatibility	LC8, LP8
Seismic Tested	No	Has Battery	No
Operating Temperature Max	55 °C	Number of Gangs	1
Number of Buttons	3	Input Voltage	24 VDC
Indoor/Outdoor	Indoor	Mounting Type	J-Box
Current Draw	2 mA	Operating Temperature	0°-55°C
Operating Humidity	5-95% RH (Non-Condensing)	Wire Connection Type	Screw Terminal
Engraving Type	Blank	Storage Temperature	23° - 176° F, -5° - 80° C
