



Multi-Weave, Rotating Eye, Cable Diameter - 1.000-1.240-inch,
Mesh Length - 52-inch, Eye Diameter - 1 3/8-inch, Break Strength -
24,600 lbs. Red.

Features & Benefits

Multi-weave pulling grips are constructed of high strength galvanized steel and are designed for pulling aluminum or copper bare conductor, wire rope and insulated cables.

Multi-weave pulling grips are available with a flexible and rotating eye, which can be attached to a swivel.

The rotating eye can turn to relieve pulling torque when tension is relaxed.

These grips are used in applications such as distribution line stringing and overhead transmission.

Description : Rotating Eye: The forged steel rotating eye will thread through sheaves and blocks without binding, but is not a swivel and will not turn under tension.

Mesh Length: 52: Eye Diameter: 1-3/8

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	Mexico
Construction	Support and Strain Relief Grips, Various Types of Pulling	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)		

Technical Information

Maximum Cable Range	1 in	Minimum Cable Range	1.24 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations
Load	Approx. Break Strength: 24600 (Gold)		