



Multi-Weave, Rotating Eye. Cable Diameter - 1.500-1.740-inch, Mesh Length - 60-inch, Eye Diameter - 1 7/8-inch, Break Strength - 30,600 lbs, Red.

## Features & Benefits

Multi-weave pulling grips are constructed of high strength galvanized steel and are designed for pulling aluminum or copper bare conductor, wire rope and insulated cables.

Multi-weave pulling grips are available with a flexible and rotating eye, which can be attached to a swivel.

The rotating eye can turn to relieve pulling torque when tension is relaxed.

These grips are used in applications such as distribution line stringing and overhead transmission.

Description : Rotating Eye: The forged steel rotating eye will thread through sheaves and blocks without binding, but is not a swivel and will not turn under tension.

Mesh Length: 60: Eye Diameter: 1-7/8

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007991956
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Technical Information

Maximum Cable Range	1.5 in	Minimum Cable Range	1.74 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations