




Wiremold  
NM2000 Sure-Snap Deep Device Box  
Part No. NM2048-2



Cover snaps onto base - no screws required. Cover has twistouts on all sides. Rectangular KO in base for extension to wall box. Used with 2700, 2800, 2900 and NM2000 Series Raceways. 4 3/4" L x 4 7/8" W x 1 3/4" D (121mm L x 124mm W x 44mm D). 2-Gang.

## Features & Benefits

Cover snaps onto base - no screws required. Cover has twistouts on all sides. Rectangular KO in base for extension to wall box.

Used with 2700, 2800, 2900 and NM2000 Series Raceways. 4 3/4" L x 4 7/8" W x 1 3/4" D (121mm L x 124mm W x 44mm D). 2-Gang.

## Specifications

### General Info

|                   |  |                    |                         |
|-------------------|--|--------------------|-------------------------|
| Product Line      | Wiremold   | UPC Number         | 786776519952            |
| Country Of Origin | United States  | Application Sector | Commercial, Residential |
| Standard          | cULus Listed Base & Blank Cover: File E90378 Guide RJBT. Multioutlet Assemblies: File E15191 Guide PVGT. Fittings: File E90377 Guide RJPR. Base & Blank Cover & Plugmold Series w/Snapcoil Harness: Meets Article 386 of NEC. Meets Section 12-3032 of CEC. Plugmold Wired Sections: Meets Article 380 of NEC. Meets Section 12-3032 of CEC. | Type               | Raceway                 |

### Dimensions

|                  |          |                   |         |
|------------------|----------|-------------------|---------|
| Product Width US | 4.875 in | Product Weight US | 0.4 lb  |
| Product Depth US | 1.75 in  | Product Length US | 4.75 in |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E90377 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

Trade Programs

---

|       |     |
|-------|-----|
| USMCA | Yes |
|-------|-----|

---

Additional Information

---

|                |     |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

---

Technical Information

---

|         |         |
|---------|---------|
| Voltage | 600.0 V |
|---------|---------|

---