



Ortronics
Rear load high density jack panel kit for 72 Clarity 6 or 5E panel jacks
Part No. PHDPJU72



Legrand® rear-loading individual jack panels utilize reduced-size Clarity® 6 and Clarity 5E panel jacks that can be terminated and snap-in from the back of the patch panel. A variety of panel configurations allow a wide choice of field configurable, easy to install horizontal cross connects. Panels are supplied without jacks. Jacks can be ordered individually or in full carton quantities of 24.

Features & Benefits

- Jacks rear load into panels: All terminations done from rear of panel.
- New positive jack latching design: Secure mounting of jacks into panel.
- High density solution: Maximizes rack space.
- Panel jacks support snap-in icons: Easy designation of ports.
- Universal wiring labels on panel jacks: Supports both T568B and T568A wiring schemes.
- Includes rear cable management: Maintains good identification and management practices.

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|--------|
| Product Line | Ortronics | Color | Black |
| UPC Number | 662875618324 | Country Of Origin | Mexico |
| Application Sector | Commercial, Industrial | Standard | RoHS |
| Warranty Type | 5-Year | Type | Panel |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 19.0 in | Product Depth US | 4.0 in |
| Product Height US | 3.5 in | | |

Additional Information

| | | | |
|-------------------------------|-----|---|-----|
| RoHS Compliant | Yes | Product Has Potential to Contribute to LEED | Yes |
| Product Environmental Profile | Yes | | |

Technical Information

| | | | |
|-----------------------------|-------|---------------|-----|
| Category Performance Rating | Cat5e | Compatibility | HDJ |
|-----------------------------|-------|---------------|-----|

| | | | |
|---------------------|------------|-----------------|----|
| Rack Units | 3 U | Number of Ports | 72 |
| Shielded/Unshielded | Unshielded | | |