

Heavy-Duty, Standard Length, Rotating Eye, K-Type. Cable Diameter - 2.000-2.490-inch, Mesh Length - 36-inch, Eye Diameter - 1 5/8-inch, Break Strength - 27,200 lbs.



Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007994407
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 2.000-2.490: Mesh Length: 36: Eye Diameter: 1-5/8
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 27,200