



**Cablofil**  
**09-6A12C-S144-12 AL 6H LDR 9RS 144L 12W (TRA)**  
Part No. P300896



The aluminum I-beam design of ITray is perfect for industrial installations with large diameter cables in long span situations, minimizing total tray width and creating a smooth transition between straight sections and fittings. A structural offset in the sidewall creates strong, mid-span splices that need fewer supports. Each splice snaps in place and stays without holding. Additionally, only four bolts are needed for each splice reducing hardware needs by 50%. These features allow Itray to be installed up to 30% faster than standard tray.

## Features & Benefits

Material: Aluminum Alloy 6063-T6

Finish: Plain

Bottom: Ldr: 1" wide I rung SB: Flat Sheet over 12" Rung Spacing.  
SC: Solid Corrugated VC: Vented Corrugated

Construction: Welded

Tray Design: Tray construction and markings are per the latest edition of NEMA Standards Publication VE1, CSA C22.2 No. 126.

Tray Grounding Capability: Classified as an equipment grounding conductor per NEC 392.60.

## Specifications

### General Info

|                    |                       |                   |               |
|--------------------|-----------------------|-------------------|---------------|
| Product Line       | Cablofil              | Finish            | Aluminum      |
| UPC Number         | 800388067615          | Country Of Origin | Mexico        |
| Application Sector | Commercial/Industrial | Standard          | UL Classified |
| Type               | Cable Tray            |                   |               |

### Dimensions

|                   |             |                   |           |
|-------------------|-------------|-------------------|-----------|
| Product Width US  | 13.5 in     | Product Weight US | 28.848 lb |
| Product Volume US | 6.941 cu ft | Product Depth US  | 144.0 in  |
| Product Height US | 6.17 in     |                   |           |

## Buy American Act Compliance

---

BAA

Yes

---