

1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V



Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure plate back wire.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007196610
Country Of Origin	Mexico	Application Sector	Industrial

StandardUL 498/20, FEDSPEC

Dimensions

Product Width US

1.32 in

Product Depth US

1.073 in

Product Height US

3.281 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber

140597

cULus Listed

Yes

Technical Information

Contact Rating

20 Amp, 120/277 VAC

Amperage

20 A

Number of Poles

Single Pole

Wire Size

#14 - #10 AWG
