



1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V

## Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure plate back wire.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007196627
Country Of Origin	Mexico	Application Sector	Industrial

---

**Standard**UL 498/20, FEDSPEC

---

**Dimensions**

---

Product Width US

1.32 in

Product Depth US

1.073 in

---

Product Height US

3.281 in

---

**Listing Agencies / 3rd Party Agencies**

---

cULus ListingNumber

140597

cULus Listed

Yes

---

**Technical Information**

---

Contact Rating

20 Amp, 120/277 VAC

Amperage

20 A

---

Number of Poles

Single Pole

Wire Size

#14 - #10 AWG

---