



Double Pole, Single Phase Switch, Back and Side Wire, HP Rated. 30 amps, 277 volts.

Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Box lug terminals. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life. Made in USA. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements. Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Color	Brown	UPC Number	785007195972
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL 20

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140597
--------------	-----	---------------------	--------

Technical Information

Wattage	2 W	Number of Poles	Double Pole
Voltage	120 V	Closed Contact Resistance	Toggle

Contact Rating

30amp, 120/277vac
