



400A 600V MALE CAM TYPE PLUG

## Features & Benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity. Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws allow greater termination torque. Copper wire provides quality strain relief. Copper shim bundles wire strands to reduce "splaying."

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007308051	Country Of Origin	Mexico
Application Sector	Commercial/Industrial	Standard	UL, cCSAus

### Technical Information

Number of Poles	Single Pole	Wire Size	2/0 - 4/0
Voltage	600 V	Environmental Conditions	Operating Temperature: Maximum continuous +75°C, minimum -40°C without impact: Flammability UL94 V2: Enclosure: NEMA Type 3R and 4