

Heavy-Duty, Standard Length, Rotating Eye, K-Type. Cable Diameter - 2.500-2.990-inch, Mesh Length - 38-inch, Eye Diameter - 1 7/8 ft, Break Strength - 33,000 lbs.



Features & Benefits

K-type pulling grips feature a double weave of galvanized steel for greater strength and added mesh contact with the cable as well as a forged steel compact rotating eye, which can be attached to a swivel.

They are designed to handle longer or heavier pulling jobs such as an installation of underground cables, communication lines and service lines.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007994414
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 2.500-2.990: Mesh Length: 38: Eye Diameter: 1-7/8
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 33,000