



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. SteriGuard provides a cost-effective way to add additional safety precautions and unequalled assurance that every feasible step has been taken in the interest of consumer protection.

Features & Benefits

| | |
|--|--|
| UL and CSA Listed | NSF (National Sanitation Foundation) Certified |
| Patent Pending | Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi |
| Anti-microbial Additive Resistant to Scuffing and Cleaning | Escherichia (E.Coli): - Log reduction > 4.8, reduced surface bacteria by > 99.99% |
| Staphylococcus (Staph), MRSA: - Log Reduction > 4.3, reduces surface bacteria by > 99.97% | Salmonella : Log Reduction > 3.6, reduces surface bacteria by > 99.97% |
| RoHS Compliant (Non-Halogenated) | Independently tested and Certified to JIS Z2801 standards |
| Resistant to High Pressure Hose-down applications | Tongue & Groove Environmental Sealing |
| Keyed Body and Cover for Alignment | NEMA Type 4, 4x, 6, 6P and IP67 Protection |
| Steriguard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care. | |

Specifications

General Info

| | | | |
|--------------|-----------------------|-------------------|---------------|
| Product Line | Pass & Seymour | Color | Yellow |
| UPC Number | 785007056952 | Country Of Origin | United States |
| Standard | UL Listed, CSA Listed | | |

Technical Information

| | |
|--------------------------|--|
| Environmental Conditions | Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized |
|--------------------------|--|