



Pass and Seymour  
100A 3 Pole 4 Wire Non-Fusible Mechanical Interlock  
Part No. PS4100MIR5W



Triple pole, Four wire, Non-Fusible Mechanical Interlock Receptacle. 100 amp, 3, 600 vac.

## Features & Benefits

- Top or Bottom feed.
- Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007015669	Country Of Origin	United States
Number of Receptacles	1	Features	Adjustable Mounting Feet
Outlet Type	Pin & Sleeve	Application Sector	Industrial
Wall Plate Included	Yes	Standard	UL Listed
Warranty Type	1-Year		

### Dimensions

Product Width US	6.88 in	Product Depth US	9.5 in
Product Height US	14.13 in		

### Technical Information

---

Operating Temperature Min	-50 °C	Connection Location	Top and Bottom
Number of Wires	4	Operating Temperature Max	60 °C
Amperage	100 A	IEC Clock Position	Clock Position 5
Enclosure Type	NEMA 12, NEMA 4X	Number of Poles	3-Way
Indoor/Outdoor	Indoor	Operating Temperature	-50°-60°C
Wire Connection Type	Screw Terminals	Voltage	600.0 V

---