




Pass and Seymour
30A 3 Pole 4 Wire Fusible Mechanical Interlock
Part No. PS430FMIR7W



Three pole, Four wire, Fusible Mechanical Interlock Receptacle, 30 amp, 3/480 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

| | | | |
|-----------------------|----------------|---------------------|---------------|
| Product Line | Pass & Seymour | Color | Gray |
| UPC Number | 785007101119 | Country Of Origin | United States |
| Number of Receptacles | 1 | Outlet Type | Pin & Sleeve |
| Application Sector | Industrial | Wall Plate Included | Yes |
| Standard | UL Listed | Warranty Type | 1-Year |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 9.13 in | Product Depth US | 8.25 in |
| Product Height US | 11.5 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------------|------------------|---------------------------|------------------|
| Operating Temperature Min | -50 °C | Connection Location | Top and Bottom |
| Number of Wires | 4 | Operating Temperature Max | 60 °C |
| Amperage | 30 A | IEC Clock Position | Clock Position 7 |
| Enclosure Type | NEMA 12, NEMA 4X | Number of Poles | 3-Way |
| Indoor/Outdoor | Indoor | Operating Temperature | -50°-60°C |
| Wire Connection Type | Screw Terminals | Voltage | 480.0 V |
