



Pass and Seymour
Fusible Safety Switch, 30 Amps
Part No. PS30FSS



Fusible Safety Switch, 30 Amps, 600 VAC. The first-ever blown-fuse indication system that's in our pacesetter Fusible Mechanical Interlocks with individual LED indicators for each line, patent-pending integral fuse pullers, and a hinged fuse-access door. P&S Fusible Safety Switches deliver the same ultra-heavy-duty construction as our Fusible Mechanical Interlocks, too. So they provide maximum protection against water, dirt, heat, and vibration and just about any other harsh condition you'll encounter.

Features & Benefits

Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage.

Captive, quick-release, stainless steel screws speed fuse removal, ensure a watertight access door seal, and won't fall out.

Heavy-duty steel-gear switch mechanism provides enhanced durability and extra-long service life.

Black/red color coding and high-visibility ON/OFF markings clearly indicate status from a distance and at any visual angle.

Durable, stainless steel cover-retaining chain makes installation and maintenance more convenient.

Corrosion-resistant, stainless steel captive screws speed installation, minimize risk of lost parts, and withstand abuse.

Time-saving LED indicators identify blown fuses at a glance.

Heavy-duty, ergonomic switch handle meets OSHA Lockout/Tagout requirements and provides plenty of grip for sure, easy operation.

Separate door for ease of changing fuses.

Specifications

General Info

Color	Gray	UPC Number	785007101010
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL, CSA

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	31169
--------------	-----	---------------------	-------

Technical Information

Number of Poles	4-Way	Voltage	600 V
Contact Configuration	1 N.O. & 1 N.C.	Connection	Hard Wired
Contact Rating	10A @ 600VAC	Frequency Rating	60 Hz

Action	Motor Disconnect Switch with Blown Fuse Indicator	Environmental Conditions	Moisture Resistance: Per UL50, Section 35, NEMA Enclosure Type 4X (watertight, hosedown), Type 12K (dusttight, falling dirt), and IP67 suitability: Flammability: UL94 5VA and VO Classification: UV Resistance: All enclosure materials are UV stable
--------	---	--------------------------	--
