



Pass and Seymour  
100A 3 Pole 4 Wire Non-Fusible Mechanical Interlock  
Part No. PS4100MIR9W



Triple pole, Four wire. Non-Fusible Mechanical Interlock Receptacle. 100 amp, 3, 240 vac.

## Features & Benefits

- Top or Bottom feed. Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate. No closure plug kits required.

## Specifications

### General Info

|                       |                |                    |                          |
|-----------------------|----------------|--------------------|--------------------------|
| Product Line          | Pass & Seymour | Color              | Gray                     |
| UPC Number            | 785007015645   | Country Of Origin  | United States            |
| Number of Receptacles | 1              | Features           | Adjustable Mounting Feet |
| Outlet Type           | Pin & Sleeve   | Application Sector | Industrial               |
| Wall Plate Included   | Yes            | Standard           | UL Listed                |
| Warranty Type         | 1-Year         |                    |                          |

### Dimensions

|                   |          |                  |        |
|-------------------|----------|------------------|--------|
| Product Width US  | 6.88 in  | Product Depth US | 9.5 in |
| Product Height US | 14.13 in |                  |        |

### Technical Information

---

|                           |                  |                           |                  |
|---------------------------|------------------|---------------------------|------------------|
| Operating Temperature Min | -50 °C           | Connection Location       | Top and Bottom   |
| Number of Wires           | 4                | Operating Temperature Max | 60 °C            |
| Amperage                  | 100 A            | IEC Clock Position        | Clock Position 9 |
| Enclosure Type            | NEMA 12, NEMA 4X | Number of Poles           | 3-Way            |
| Indoor/Outdoor            | Indoor           | Operating Temperature     | -50°-60°C        |
| Wire Connection Type      | Screw Terminals  | Voltage                   | 248.0 V          |

---