



Pass and Seymour
100A 4 Pole 5 Wire Fusible Mechanical Interlock
Part No. PS5100FMIR7W



Four pole, Five wire, Fusible Mechanical Interlocking Receptacle.
100 amp, 3Y, 277/480 vac.

Features & Benefits

Top or Bottom feed.

Unit shipped with no holes drilled: a top and bottom feed spot drill is provided for locating hole saw or knockout.

End user decides at installation whether top or bottom feed is appropriate.

No closure plug kits required.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007101300	Country Of Origin	United States
Number of Receptacles	1	Outlet Type	Pin & Sleeve
Application Sector	Industrial	Wall Plate Included	Yes
Standard	UL Listed	Warranty Type	1-Year

Dimensions

Product Width US	11.13 in	Product Depth US	11.06 in
Product Height US	28.31 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E31169	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Operating Temperature Min	-50 °C	Connection Location	Top and Bottom
Number of Wires	5	Operating Temperature Max	60 °C
Amperage	100 A	IEC Clock Position	Clock Position 7
Enclosure Type	NEMA 12, NEMA 4X	Number of Poles	4-Way
Indoor/Outdoor	Indoor	Operating Temperature	-50°-60°C
Wire Connection Type	Screw Terminals	Voltage	277.0 V
