



Pass and Seymour  
15A 125V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Brown  
Part No. PS5262



Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

## Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Strap tabs wrap around face to prevent strap from separating from face and back body.

High strength nylon face.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007859874	Country Of Origin	Mexico
Number of Receptacles	2	Application Sector	Commercial
Standard	cULus UL498, CSA C22.2 No. 42, FEDSPEC	Type	Outlet

---

## Dimensions

---

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

---

Product Height US	2.635 in
-------------------	----------

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
---------------------	--------------------------	------------	--------------------

---

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

---

Amperage	15 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

---

Environmental Conditions	Flammability: UL94 V2		
--------------------------	-----------------------	--	--

---