



Pass and Seymour
15A 125V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Red
Part No. PS5262RED



Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Strap tabs wrap around face to prevent strap from separating from face and back body.

High strength nylon face.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007859904	Country Of Origin	Mexico
Number of Receptacles	2	Application Sector	Commercial
Standard	cULus UL498, CSA C22.2 No. 42, FEDSPEC	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Environmental Conditions	Flammability: UL94 V2		
