



Pass and Seymour  
Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory  
Part No. PS5362I



Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Brown

## Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

High strength nylon face.

Eight back wire holes.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

Color	Ivory	UPC Number	785007859935
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Commercial	Standard	cULus UL498, CSA C22.2 No. 42

### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

---

## Technical Information

---

Number of Poles	Double Pole	Voltage	125 V
Connection	Back and side wire	Dielectric Strength	Withstands 2000V minimum
Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	Wire Size	#14 - #10
Number of Wires	3	Environmental Conditions	Flammability: UL94 V2

---