



Pass and Seymour Non-Fusible Safety Switch, 60 Amps Part No. PS60SS



Non-Fusible Safety Switch, 60 Amps, 600 VAC. The first non-metallic NEMA 4X Non-Fusible Safety Switch line UL Listed as Suitable as Motor Disconnect per NEC Article 430.109(A)(6). P&S Non-Fusible Safety Switches feature extra-tough components, including an impact-resistant Valox NEMA 4X enclosure. And an innovative design that delivers safe, sure operation under the worst conditions.

Features & Benefits

Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage.	Nonconductive, watertight, corrosion-, heat-, and impact-resistant thermoplastic enclosure ensures NEMA 4X and 12 ratings. Withstands the harshest industrial environments.
Corrosion-resistant, stainless steel captive screws speed installation, minimize risk of lost parts, and withstand abuse.	Adjustable mounting feet can be moved to center of unit for instant strut- or pole-mounting without special brackets or harnesses.
Durable, stainless steel coverretaining chain makes installation and maintenance more convenient.	Heavy-duty, ergonomic switch handle meets OSHA Lockout/Tagout provisions and provides plenty of grip for sure, easy operation.
Black/red color coding and high-visibility ON/OFF markings clearly indicate status from a distance and at any visual angle.	Switch entry into the enclosure is offset to the side and sealed to provide enhanced water resistance.
Bottom and top wiring access options. No unnecessary openings to compromise water resistance.	Top mount auxiliary contact enables additional control functions or signal lights.
Certified for IP69 applications.	

Specifications

General Info

Color	Gray	UPC Number	785007150100
Country Of Origin	United States	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	31169
--------------	-----	---------------------	-------

Technical Information

Number of Poles	3-Way	Voltage	600 V
-----------------	-------	---------	-------