



Pass and Seymour Heavy-Duty Hospital Grade Smooth Face Receptacles, Back & Side Wire, 15A, 125V, Gray Part No. PS8200HSGRY



Heavy-Duty Hospital Grade Smooth Face Duplex Receptacle Back & Side Wire 15amp 125volt Brown

Features & Benefits

| | |
|--|---|
| Heavy-duty, brass strap for added strength and ground conductivity. | .032 inch thick, brass, triple-wipe power contacts for lasting retention. |
| Strap tabs wrap around face to prevent strap from separating from face and back body. | Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring. |
| Two drive screws anchor strap to back body and face. | Tri-drive brass terminal screws. |
| Internal screw-pressure-plate back and side wire capability. | Two back wire holes for more wiring flexibility. |
| Auto-ground clip assures positive ground. | Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up. |
| For covering patents, see www.legrand.us/patents . | For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here . |

Specifications

General Info

| | | | |
|--------------------|---------------|--------------|-------------------------|
| Color | Gray | UPC Number | 785007307160 |
| Country Of Origin | United States | Product Line | Pass & Seymour |
| Application Sector | Commercial | Standard | UL498, CSA C22.2 No. 42 |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|--------------------|---|---------------------|--------------------------|
| Number of Poles | Double Pole | Voltage | 125 V |
| Connection | Back and side wire | Dielectric Strength | Withstands 2000V minimum |
| Temperature Rating | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact | Wire Size | #14 - #10 |

Number of
Wires 3

Environmental Conditions

Flammability: UL94 V2
