



Pass and Seymour  
Fusible Safety Switch, 60As  
Part No. PS60FSS



Fusible Safety Switch, 60 Amps, 600 VAC. The first-ever blown-fuse indication system that's in our pacesetter Fusible Mechanical Interlocks with individual LED indicators for each line, patent-pending integral fuse pullers, and a hinged fuse-access door. Pass and Seymour Fusible Safety Switches deliver the same ultra-heavy-duty construction as our Fusible Mechanical Interlocks, too. So they provide maximum protection against water, dirt, heat, and vibration and just about any other harsh condition you'll encounter.

## Features & Benefits

Compact design fits in most I-beams to provide mounting versatility, easy access, and reduced possibility of impact damage.

Captive, quick-release, stainless steel screws speed fuse removal, ensure a watertight access door seal, and won't fall out.

Heavy-duty steel-gear switch mechanism provides enhanced durability and extra-long service life.

Black/red color coding and high-visibility ON/OFF markings clearly indicate status from a distance and at any visual angle.

Durable, stainless steel cover-retaining chain makes installation and maintenance more convenient.

Corrosion-resistant, stainless steel captive screws speed installation, minimize risk of lost parts, and withstand abuse.

Time-saving LED indicators identify blown fuses at a glance.

Heavy-duty, ergonomic switch handle meets OSHA Lockout/Tagout requirements and provides plenty of grip for sure, easy operation.

Separate door for ease of changing fuses.

## Specifications

### General Info

|                   |                |                    |               |
|-------------------|----------------|--------------------|---------------|
| Product Line      | Pass & Seymour | Color              | Gray          |
| Finish            | Matte          | UPC Number         | 785007101027  |
| Country Of Origin | United States  | Application Sector | Industrial    |
| Standard          | UL Listed      | Type               | Safety Switch |

### Listing Agencies / 3rd Party Agencies

---

|                     |       |              |     |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | 31169 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

---

### Technical Information

---

|                   |                                                                                                                                                                                                                                                                  |            |           |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|-----------|
| Horsepower Rating | 10 HP @ 208 VAC, 10 HP @ 240 VAC, 15 HP @ 277 VAC, 20 HP @ 3 $\phi$ 240 VAC, 20 HP @ 3 $\phi$ 480 VAC, 20 HP @ 3 $\phi$ 600 VAC, 20 HP @ 3 $\phi$ Y 120/208 VAC, 20 HP @ 480 VAC, 3 HP @ 120 VAC, 40 HP @ 3 $\phi$ Y 277/480 VAC, 50 HP @ 3 $\phi$ Y 347/600 VAC | Connection | Hardwired |
|-------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|-----------|

---

|          |      |                |                                 |
|----------|------|----------------|---------------------------------|
| Amperage | 60 A | Enclosure Type | NEMA 12,<br>NEMA 4X,<br>Plastic |
|----------|------|----------------|---------------------------------|

---

|                 |       |           |               |
|-----------------|-------|-----------|---------------|
| Number of Poles | 4-Way | Wire Size | #14 - #10 AWG |
|-----------------|-------|-----------|---------------|

---

|                           |                                |                 |        |
|---------------------------|--------------------------------|-----------------|--------|
| Maximum Horsepower Rating | 50 HP @ 3 $\phi$ Y 347/600 VAC | Wiring Location | Bottom |
|---------------------------|--------------------------------|-----------------|--------|

---

|         |              |
|---------|--------------|
| Voltage | 120 to 600 V |
|---------|--------------|

---