



Heavy-Duty Hospital Grade Smooth Face Duplex Receptacle Back & Side Wire 15amp 125volt Brown

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Two drive screws anchor strap to back body and face.

Internal screw-pressure-plate back and side wire capability.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

Smooth face version features an impact-resistant nylon face for ease of cleaning and less dirt build-up.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Country Of Origin	United States	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42		

Dimensions

Product Width US	1.322 in	Product Depth US	1.18 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Voltage	125.0 V
Environmental Conditions	Flammability: UL94 V2		
