



Pass and Seymour
Sloped-Roof Stainless Steel Safety Switch with Auxiliary Contact, 60A
Part No. PSDS60HPAXSR



60 Amps HP Sloped-Roof Stainless Steel Safety Switch with Auxiliary Contact. Legrand's 316-Grade Sloped-Roof Stainless Steel Safety Switches are designed to provide superior corrosion resistance in harsh environments like food and beverage processing plants where wash down/hose down at extreme temperatures is a daily necessity, as well as environments where salts, acids, and chemicals are prevalent. Legrand's Sloped-Roof Stainless Steel Safety Switches with NEMA 4X/12, IP66, 67, and 69K ratings are the best solution for durability and personnel safety in any environment.

Features & Benefits

Type 316 grade stainless steel provides superior resistance to corrosion.

Certified by the National Sanitation Foundation (NSF) for hygiene requirements in food & beverage processing.

15: sloped roof helps to facilitate run-off and minimize the harborage of contaminants.

Water- and dust-tight enclosure rated NEMA 3R, 4, 4X, 12K and IP66, 67, 69 for protection against high-pressure, high-temperature water from multiple directions.

OSHA-compliant Lockout/Tagout.

Captive cover screws.

Inability to remove cover when in ON position.

6 conduit entry points for flexible installation options.

Can accommodate up to 3 sets of auxiliary contacts for control circuit applications.

3/4" standoffs on mounting feet allow adequate space for runoff and inspection behind the switch.

High-visibility yellow and red handle can be padlocked to meet OSHA lockout/tagout requirements.

Multiple drill points for ease of installation (each side and back).

No labels on cover, stamped-in ON/OFF.

Compact footprint.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007133677
Country Of Origin	United States	Application Sector	Industrial
Type	Safety Switch		

Dimensions

Product Width US 9.13 in

Product Depth US

6.31 in

Product Height US 12.38 in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Horsepower Rating 15 HP @ 3 ϕ 240 VAC, 15 HP @ 480 VAC, 15 HP @ 600 VAC, 3 HP @ 120 VAC, 30 HP @ 3 ϕ 480 VAC, 30 HP @ 3 ϕ 600 VAC, 7-1/2 HP @ 240 VAC, 7-1/2 HP @ 277 VAC

Connection

Hardwired

Amperage

60 A

Enclosure Type

NEMA 12,
NEMA 4X,
Stainless
Steel

Wire Size

#14 - #10 AWG

Maximum Horsepower Rating

30 HP @ 3 ϕ
600VAC

Wiring Location

Bottom, Top

Voltage

120 to 600 V
