



100 Amps Stainless Steel Safety Switch. Legrand's 316-Grade Stainless Steel Safety Switches are designed to provide superior corrosion resistance in harsh environments like food and beverage processing plants where wash down/hose down at extreme temperatures is a daily necessity, as well as environments where salts, acids, and chemicals are prevalent. Legrand's Stainless Steel Safety Switches with NEMA 4X/12, IP66, 67, and 69K ratings are the best solution for durability and personnel safety in any environment.

## Features & Benefits

Type 316 grade stainless steel provides superior resistance to corrosion.

Certified by the National Sanitation Foundation (NSF) for hygiene requirements in food & beverage processing.

3/4" standoffs on mounting feet allow adequate space for runoff and inspection behind the switch.

High-visibility yellow and red handle can be padlocked to meet OSHA lockout/tagout requirements.

Multiple drill points for ease of installation (each side and back).

Inability to remove cover when in ON position.

Compact footprint.

8 conduit entry points for flexible installation options.

Can accommodate up to 3 sets of auxiliary contacts for control circuit applications.

Water- and dust-tight enclosure rated NEMA 3R, 4, 4X, 12K and IP66, 67, 69 for protection against high-pressure, high-temperature water from multiple directions.

OSHA-compliant Lockout/Tagout.

No labels on cover, stamped-in ON/OFF.

Captive cover screws.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007133684
Country Of Origin	United States	Application Sector	Industrial
Type	Safety Switch		

### Dimensions

---

Product Width US 7.3 in

Product Depth US

7.1 in

---

Product Height US 11.6 in

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed Yes

---

### Technical Information

---

Horsepower Rating 15 HP @ 240 VAC, 15 HP @ 277 VAC, 25 HP @ 3∅  
240 VAC, 30 HP @ 480 VAC, 30 HP @ 600 VAC, 5 HP  
@ 120 VAC, 50 HP @ 3∅ 480 VAC, 50 HP @ 3∅ 600  
VAC

Connection

Hardwired

---

Amperage

100 A

Enclosure Type

NEMA 12,  
NEMA 4X,  
Stainless  
Steel

---

Wire Size

#14 - #10 AWG

Maximum Horsepower Rating

50 HP @ 3∅  
600VAC

---

Wiring Location

Bottom, Top

Voltage

120 to 600 V

---