



PlugTail® Decorator Spec Grade Receptacles, 20A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

|                                                                                                                                                                                                                               |                                                                                                                                     |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------|
| .036 inch thick, brass, triple-wipe power contacts for lasting retention.                                                                                                                                                     | No exposed terminals create a finger safe application before, during, and after installation.                                       |
| Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.                                                                                                                | Crimped and welded contacts.                                                                                                        |
| Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.                                                                                                | Pre-stripped connector leads fasten to conductors, easier than standard pigtails.                                                   |
| Auto-ground clip assures positive ground.                                                                                                                                                                                     | For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .                                      |
| Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact | PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only |

## Specifications

### General Info

|                   |                    |                       |                         |
|-------------------|--------------------|-----------------------|-------------------------|
| Product Line      | Pass & Seymour     | Color                 | Gray                    |
| Country Of Origin | Mexico             | Number of Receptacles | 2                       |
| Outlet Type       | Commercial, Indoor | Application Sector    | Commercial              |
| Standard          | cULus UL498        | Warranty Type         | 1-Year Limited Warranty |
| Type              | Outlet             |                       |                         |

---

## Dimensions

---

|                   |         |                  |          |
|-------------------|---------|------------------|----------|
| Product Width US  | 1.5 in  | Product Depth US | 0.625 in |
| Product Height US | 2.75 in |                  |          |

---

## Listing Agencies / 3rd Party Agencies

---

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

---

## Technical Information

---

|                          |                          |                 |         |
|--------------------------|--------------------------|-----------------|---------|
| Dielectric Strength      | Withstands 2000V minimum | Number of Wires | 3       |
| Temperature Rating       | -40° - 60° C             | Amperage        | 20 A    |
| Number of Poles          | Double Pole              | Wire Size       | 12 AWG  |
| Indoor/Outdoor           | Indoor                   | Voltage         | 125.0 V |
| Environmental Conditions | Flammability: UL94 V2    |                 |         |

---