



PlugTail® Industrial Extra Heavy-Duty Spec Grade Receptacles, 15A, 125A

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

- No exposed terminals create a finger safe application before, during, and after installation.
- Crimped and welded contacts.
- Large brass contacts snugly terminate on device blade terminals.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).
- PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007860177	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498, FEDSPEC

Dimensions

Product Width US	1.625 in	Product Depth US	0.866 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Technical Information			
Phase	Three	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG		