



20A GFCI works with the existing three-wire PlugTail connectors creating a non-feed thru application for facility owners. At rough-in, just install the same right-angle connector for GFCI and receptacle openings. PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven	SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected
Faster, more reliable installation	No exposed terminals create a finger-safe application before, during, and after installation
Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector	GFCI works with the existing 3-wire PlugTail connectors creating a non-feed-through application for facility
Zinc-plated steel mounting strap	

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007048186	Country Of Origin	China
Number of Receptacles	2	Features	Self-Test
Outlet Type	GFCI	Application Sector	Commercial, Residential
Wall Plate Included	Yes	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.72 in	Product Depth US	1.2 in
------------------	---------	------------------	--------

Product Height US	4.2 in
-------------------	--------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Connection Location	Back Only	Frequency Rating	60 Hz
Connection	Built-in Connector	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Wire Connection Type	PlugTail	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		