



Pass and Seymour
PlugTail® Hospital Grade Extra Heavy Duty Surge Protective Duplex Receptacle, Ivory
Part No. PT8200ISP



PlugTail®Hospital Grade Extra Heavy-DutySurge ProtectiveDuplexReceptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). 15 A 125 V, Ivory . For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

| | |
|---|--|
| .036 inch thick, brass, triple-wipe power contacts for lasting retention. | Plated steel wrap strap design for maximum durability and corrosion resistance. |
| No exposed terminals create a finger safe application before, during, and after installation. | Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. |
| Crimped and welded contacts. | Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. |
| Large brass contacts snugly terminate on device blade terminals. | Pre-stripped connector leads fasten to conductors, easier than standard pigtailed. |
| Auto-ground clip assures positive ground. | For covering patents, see www.legrand.us/patents . |

Specifications

General Info

| | | | |
|--------------------|------------------------|-------------------|--|
| Product Line | Pass & Seymour | Country Of Origin | China |
| Application Sector | Residential/Commercial | Standard | CSA Listed, cUL, UL Listed, RoHS, FSUL |

Dimensions

| | | | |
|-------------------|---------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.625 in |
| Product Height US | 2.75 in | | |

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

| | | | |
|------------|--------------------|--------------------------|--------------------|
| Phase | Single | Frequency Rating | 60 Hz |
| Connection | Built-In Connector | Class | IG |
| Amperage | 15 A | Type of Indicators | Audible Alarm, LED |
| Voltage | 125.0 V | Environmental Conditions | UL94 V2 |
