



Pass and Seymour  
**PlugTail® Heavy Duty Spec Grade Plug Load Controllable Receptacle, 20A, 125V, Gray**  
 Part No. PT26352SCCTGRY



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters.

## Features & Benefits

- .032 inch thick, brass, triple-wipe power contacts for lasting retention. Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC. Auto-ground clip assures positive ground.
- Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications. For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#). Wire Size: #12 AWG THHN

## Specifications

### General Info

|                   |                                    |                    |            |
|-------------------|------------------------------------|--------------------|------------|
| Product Line      | Pass & Seymour                     | Color              | Gray       |
| Country Of Origin | Mexico                             | Application Sector | Commercial |
| Standard          | UL Listed, CSA Listed, cULus, FSUL |                    |            |

### Dimensions

|                   |         |                  |          |
|-------------------|---------|------------------|----------|
| Product Width US  | 1.5 in  | Product Depth US | 0.625 in |
| Product Height US | 2.75 in |                  |          |

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed      Yes

---

## Technical Information

---

|                     |                          |       |        |
|---------------------|--------------------------|-------|--------|
| Dielectric Strength | Withstands 2000V minimum | Phase | Single |
|---------------------|--------------------------|-------|--------|

---

|            |          |                 |   |
|------------|----------|-----------------|---|
| Connection | PlugTail | Number of Wires | 3 |
|------------|----------|-----------------|---|

---

|                    |              |          |      |
|--------------------|--------------|----------|------|
| Temperature Rating | -40° - 60° C | Amperage | 20 A |
|--------------------|--------------|----------|------|

---

|                 |             |           |        |
|-----------------|-------------|-----------|--------|
| Number of Poles | Double Pole | Wire Size | 12 AWG |
|-----------------|-------------|-----------|--------|

---

|         |         |                          |         |
|---------|---------|--------------------------|---------|
| Voltage | 125.0 V | Environmental Conditions | UL94 V2 |
|---------|---------|--------------------------|---------|

---