



Pass and Seymour
PlugTail® Heavy Duty Spec Grade Plug Load Controllable Receptacle, 20A, 125V, Ivory
 Part No. PT26352SCCTI



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC.
- Auto-ground clip assures positive ground.
- Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
- Wire Size: #12 AWG THHN

Specifications

General Info

| | | | |
|-------------------|------------------------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL Listed, CSA Listed, cULus, FSUL | | |

Dimensions

| | | | |
|-------------------|---------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 0.625 in |
| Product Height US | 2.75 in | | |

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

| | | | |
|---------------------|--------------------------|-------|--------|
| Dielectric Strength | Withstands 2000V minimum | Phase | Single |
|---------------------|--------------------------|-------|--------|

| | | | |
|------------|----------|-----------------|---|
| Connection | PlugTail | Number of Wires | 3 |
|------------|----------|-----------------|---|

| | | | |
|--------------------|--------------|----------|------|
| Temperature Rating | -40° - 60° C | Amperage | 20 A |
|--------------------|--------------|----------|------|

| | | | |
|-----------------|-------------|-----------|--------|
| Number of Poles | Double Pole | Wire Size | 12 AWG |
|-----------------|-------------|-----------|--------|

| | | | |
|---------|---------|--------------------------|---------|
| Voltage | 125.0 V | Environmental Conditions | UL94 V2 |
|---------|---------|--------------------------|---------|
