



Pass and Seymour
PlugTail® Heavy Duty Spec Grade Plug Load Controllable Receptacle, 20A, 125V, Ivory
Part No. PT26352SCCTI



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters.

Features & Benefits

- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC.
- Auto-ground clip assures positive ground.
- Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
- Wire Size: #12 AWG THHN

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007496437	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL Listed, CSA Listed, cULus, FSUL, FEDSPEC

Dimensions

Product Width US	1.5 in	Product Depth US	0.625 in
------------------	--------	------------------	----------

Product Height US	2.75 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Phase	Single
---------------------	--------------------------	-------	--------

Connection	PlugTail	Number of Wires	3
------------	----------	-----------------	---

Temperature Rating	-40° - 60° C	Amperage	20 A
--------------------	--------------	----------	------

Number of Poles	Double Pole	Wire Size	12 AWG
-----------------	-------------	-----------	--------

Environmental Conditions	UL94 V2
--------------------------	---------