



Legrand

PlugTail® Tamper-Resistant Heavy-Duty Spec Grade Plug Load Controllable Receptacle, 15A, 125V, Gray
Part No. PTTR5262SCCHGRY



These durable, dependable receptacles feature a permanently marked, differentiated solution that meets all necessary code requirements. For detailed PlugTail® information, visit our PlugTail® Headquarters. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

.032 inch thick, brass, triple-wipe power contacts for lasting retention.	Plated steel wrap strap design for maximum durability and corrosion resistance.
No exposed terminals create a finger safe application before, during, and after installation.	Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
Dual mechanical shutter system to help prevent insertion of foreign objects (TR models).	Permanent controlled markings on face of receptacle compliant with ASHRAE 90.1, CA Title 24, and NEC.
Auto-ground clip assures positive ground.	Half-controlled versions include welded, pre-wired lead that control top half of receptacle for split circuit applications.
For covering patents, see www.legrand.us/patents .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Specifications

General Info

Color	Gray
UPC Number	785007051698
Country Of Origin	Mexico
Product Line	Pass & Seymour
Application Sector	Commercial
Standard	UL Listed, CSA Listed, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Poles	Double Pole
Voltage	125 V
Connection	PlugTail

Dielectric Strength	Withstands 2000V minimum
Phase	Single
Temperature Rating	Maximum continuous +60°C, minimum -40° without impact
Wire Size	#12 AWG THHN
Number of Wires	3
Environmental Conditions	UL94 V2
