



Pass and Seymour  
**PlugTail® 15A 125V Spec-Grade Duplex Receptacle, Gray**  
Part No. PT5262GRY



PlugTail® Spec Grade Receptacles, 15A, 125V PlugTail® devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

## Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Illuminated face indicates power to receptacle and makes it easy to identify receptacle in dark applications.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Crimped and welded contacts.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

## Specifications

### General Info

|                       |                 |                    |            |
|-----------------------|-----------------|--------------------|------------|
| Product Line          | Pass & Seymour  | Color              | Gray       |
| UPC Number            | 785007091601    | Country Of Origin  | Mexico     |
| Number of Receptacles | 2               | Application Sector | Commercial |
| Standard              | UL 498, FEDSPEC | Type               | Outlet     |

---

Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in |                  |         |

Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

|           |             |                 |             |
|-----------|-------------|-----------------|-------------|
| Phase     | Three       | Number of Wires | 3           |
| Amperage  | 15 A        | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Indoor/Outdoor  | Indoor      |